

DALI SENSOR LS/PD CI G2

DALI SENSOR LS/PD CI G2 | 传感器



产品特点

- Light and presence sensor for ceiling integration
- 通过无源红外零件进行存在检测
- 安装高度：2...5 m
- 双色 LED 功能指示器
- 天花板安装用适配器

产品优势

- Flat design, very small structural height
- Simple and fast installation via wire springs
- DALI-2 certified
- DALI Bus powered (No mains connection necessary)
- Multiple sensors connectable to the same DALI line
- 利用集成式百叶窗，可在 40...90°之间调整存在检测角
- Integreable in light- and building management systems supporting DALI-2 sensors

应用领域

- 适用于室内应用
- 独立办公室
- 开放式大办公室
- 教室
- 会议室
- 走廊


产品数据表

技术参数

电参数

Required DALI current (typical)	6 毫安
Peak DALI current	16 毫安
Maximum start-up time (DALI)	600 ms

尺寸和重量



长度	80.0 mm
安装孔距, 宽度	73 mm
产品重量	95.00 g

温度

环境温度范围	-20...+50 °C
--------	--------------

功能

可调光	否
调光界面	DALI-2
最大安装高度	5 m
探测区域	7 m²
探测角度	40...90 °
工作范围,光传感器	20...800 lx
安装类型	隐藏式

认证与标准

防护类型	IP20
------	------

物流数据

商品编码	90318080000
------	-------------

产品数据表

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	04-10-2023
Primary Article Identifier	4062172072083
Candidate List Substance 1	Lead titanium zirconium oxide
CAS No. of substance 1	12626-81-2
Candidate List Substance 2	Lead
CAS No. of substance 2	7439-92-1
Safe Use Instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.
Declaration No. in SCIP database	bc731bf9-1aff-4034-a5c1-60231a854935

下载数据

文件	
	User instruction DALI2 SENSOR LSPD CI
	统一宣言 DALI G2 Sensor Coupler CE 4202657 03 060823
	CAD数据 DALI SENSOR LS PD CI G2 IGS 110820
	CAD数据 DALI SENSOR LS PD CI G2 STEP 110820
	CAD数据2 DALI SENSOR LS PD CI G2 2PDF 110820
	CAD数据3 DALI SENSOR LS PD CI G2 CAD3PDF 110820

物流数据

产品代码	产品描述	包装单位 (件/单位)	尺寸 (长 x 宽 x 高)	体积	毛重
4062172072083	DALI SENSOR LS/PD CI G2	箱 10	217 mm x 217 mm x 180 mm	8.48 dm³	1229.00 g

这里所提到的产品编码代表最小订购数量。一个整件包装含有一个或多个单一产品。请您在下单时，按一个或多个整件数下单。

免责声明

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.